

| CATALOG NUMBER | DESCRIPTION | UPC CODE | WEIGHT | CASE QTY | PALLET QTY | DISTRIBUTION CTRS | | | | | |
|--|---|--------------|--------|----------|------------|-------------------|----|----|----|----|---|
| | | | | | | NJ | IL | TX | CA | GA | |
| SLIPFITTER - HIGH PRESSURE SODIUM | | | | | | | | | | | |
| XS15 | 150W HPS MULTI-TAP W/LAMP WARRIOR SLIPFITTER MOUNT BRONZE | 662400117452 | 30 | 1 | 16 | | | • | | | |
| HPWR-65S-250/400-MT | 250/400W HPS MULTI-TAP CWA SLIPFITTER BRONZE | 662400124542 | 29.75 | 1 | 16 | • | | | | | |
| XS25 | 250W HPS MULTI-TAP SLIPFITTER W/LAMP BRONZE | 662400117469 | 33 | 1 | 16 | | | | | • | + |
| HPWR-65S-400-480V | 400W HPS 480V SLIPFITTER BRONZE | 662400899587 | 37 | 1 | 20 | | | | | • | |
| HPWR-65S-400-MT | 400W HPS MULTI-TAP SLIPFITTER BRONZE | 662400124474 | 37 | 1 | 16 | | | | | • | |
| XS40 | 400W HPS MULTI-TAP SLIPFITTER W/LAMP BRONZE | 662400117476 | 34.6 | 1 | 20 | | | • | | • | + |
| ACCESSORY | | | | | | | | | | | |
| FA5BZ | POLE TOP FITTER 2" PIPE | 662400115762 | 3.7 | 1 | 630 | | | • | | | |
| TV/WR | TOP VISOR BRONZE WARRIOR | 662400971870 | 1 | 1 | 126 | | | | | • | + |
| VG/WR | VANDAL GUARD | 662400971863 | 1 | 1 | 150 | | | | | • | + |
| WG/WR | WIRE GUARD WARRIOR | 662400971924 | 0.8 | 1 | 150 | | | | | • | + |

NIGHTHAWK

NJ IL TX CA GA



SLIPFITTER - METAL HALIDE

| | | | | | | | | | | | |
|--------------------|---|--------------|------|---|----|--|---|---|---|---|---|
| MHNKS25 | 250W MH MULTI-TAP SLIPFITTER W/LAMP BRONZE | 623961565335 | 46 | 1 | 8 | | | | | | |
| MHNKS40 | 400W MH MULTI-TAP SLIPFITTER W/LAMP BRONZE | 623961565212 | 50.8 | 1 | 16 | Available while supplies last, please consult your Cooper Lighting Representative. | | | | | |
| MHNK-S76-1000-480V | 1000W MH 480V SLIPFITTER BRONZE | 662400118794 | 61.8 | 1 | 8 | | | | | | |
| MHNKS1K | 1000W MH MULTI-TAP SLIPFITTER W/LAMP BRONZE | 623961565205 | 68 | 1 | 12 | • | • | • | • | • | + |

YOKE - METAL HALIDE

| | | | | | | | | | | | |
|--------------------|---------------------------------------|--------------|------|---|----|--|---|---|---|---|---|
| MHNKY40 | 400W MH MULTI-TAP YOKE W/LAMP BRONZE | 623961565342 | 58 | 1 | 8 | Available while supplies last, please consult your Cooper Lighting Representative. | | | | | |
| MHNK-Y76-1000-480V | 1000W MH 480V CWA YOKE BRONZE | 662400118787 | 64.8 | 1 | 12 | | | | | | |
| MHNKY1K | 1000W MH MULTI-TAP YOKE W/LAMP BRONZE | 623961565328 | 70 | 1 | 12 | • | • | • | • | • | + |

SLIPFITTER - PULSE START METAL HALIDE

| | | | | | | | | | | | |
|---------|--|------------------|------|---|----|--|--|--|--|---|---|
| MPNKS32 | 320W MP MULTI-TAP SLIPFITTER W/LAMP BRONZE | 623961009402 (E) | 50.8 | 1 | 16 | | | | | • | + |
| MPNKS40 | 400W MP MULTI-TAP SLIPFITTER W/LAMP BRONZE | 623961755132 (E) | 50.8 | 1 | 16 | | | | | • | + |

YOKE - PULSE START METAL HALIDE

| | | | | | | | | | | | |
|---------|--------------------------------------|------------------|----|---|---|--|--|---|--|---|---|
| MPNKY32 | 320W MP MULTI-TAP YOKE W/LAMP BRONZE | 623961009419 (E) | 58 | 1 | 8 | | | • | | • | + |
| MPNKY40 | 400W MP MULTI-TAP YOKE W/LAMP BRONZE | 623961755170 (E) | 58 | 1 | 8 | | | • | | • | + |

SLIPFITTER - HIGH PRESSURE SODIUM

| | | | | | | | | | | | |
|--------------------|--|--------------|------|---|----|---|--|--|--|---|---|
| HPNKS40 | 400W HPS MULTI-TAP SLIPFITTER W/LAMP BRONZE | 623961565175 | 53.6 | 1 | 12 | | | | | • | + |
| HPNK-S76-1000-480V | 1000W HPS 480V SLIPFITTER BRONZE | 662400920946 | 59.4 | 1 | 12 | | | | | • | |
| HPNKS1K | 1000W HPS MULTI-TAP SLIPFITTER W/LAMP BRONZE | 623961565168 | 62.4 | 1 | 12 | • | | | | • | + |

YOKE - HIGH PRESSURE SODIUM

| | | | | | | | | | | | |
|--------------------|--|--------------|------|---|----|--|--|---|--|---|---|
| HPNKY40 | 400W HPS MULTI-TAP YOKE W/LAMP BRONZE | 623961565199 | 54.6 | 1 | 8 | | | | | • | + |
| HPNK-Y76-1000-480V | 1000W HPS 480V YOKE BRONZE | 662400129912 | 63.6 | 1 | 12 | | | | | • | |
| HPNKY1K | 1000W HPS MULTI-TAP YOKE W/LAMP BRONZE | 623961565182 | 64.2 | 1 | 8 | | | • | | • | + |

ACCESSORY

| | | | | | | | | | | | |
|-------|--------------------------------------|--------------|-----|----|-----|--|--|--|--|---|---|
| SV/NK | DOUBLE SIDE VISOR BRONZE NIGHTHAWK | 662400121091 | 2.6 | 1 | 120 | | | | | • | + |
| TV/NK | TOP OR BOTTOM VISOR BRONZE NIGHTHAWK | 662400121077 | 3 | 1 | 66 | | | | | • | + |
| VS/NK | VANDAL SHIELD NIGHTHAWK, 400W MAX | 662400121145 | 2 | 12 | 150 | | | | | • | + |

EAGLE

NJ IL TX CA GA



METAL HALIDE

| | | | | | | | | | | | |
|----------------|---|--------------|------|---|----|--|--|---|--|---|--|
| MHXL-3-1000-MT | 1000W MH MULTI-TAP NEMA TYPE III, BALLAST POD ONLY, NO REFLECTORS | 662400917076 | 36.6 | 9 | 36 | | | | | • | |
| MHXL-4-1000-MT | 1000W MH MULTI-TAP NEMA TYPE IV, BALLAST POD ONLY, NO REFLECTORS | 662400120469 | 37 | 1 | 36 | | | • | | • | |
| MHXL-5-1000-MT | 1000W MH MULTI-TAP NEMA TYPE V, BALLAST POD ONLY, NO REFLECTORS | 662400120476 | 36.6 | 1 | 36 | | | • | | • | |
| MHXL-6-1000-MT | 1000W MH MULTI-TAP NEMA TYPE VI, BALLAST POD ONLY, NO REFLECTORS | 662400917083 | 37.2 | 9 | 36 | | | | | • | |
| MHXL-3-1500-MT | 1500W MH MULTI-TAP NEMA TYPE III, BALLAST POD ONLY, NO REFLECTORS | 662400918301 | 42 | 9 | 36 | | | | | • | |
| MHXL-4-1500-MT | 1500W MH MULTI-TAP NEMA TYPE IV, BALLAST POD ONLY, NO REFLECTORS | 662400120483 | 41.8 | 1 | 36 | | | • | | • | |