

BIZLINE RXP PART#	CANTEX PART#	CARLON PART #	IPEX Part#	I2of5	SIZE	BIZLINE DESCRIPTION	STD. PKG.
SCHEDULE 40 & 80 FITTINGS							
COUPLINGS							
050CPL	6141623	E940D	EC10	30088700958280	½"	1/2-CONDUIT-SCH-40-CPLG	200
075CPL	6141624	E940E	EC15	30088700958198	¾"	3/4-CONDUIT-SCH-40-CPLG	125
100CPL	6141625	E940F	EC20	30088700958204	1"	1-IN-CONDUIT-SCH-40-CPLG	70
125CPL	6141626	E940G	EC25	30088700958211	1¼"	1-1/4-CONDUIT-SCH-40-CPLG	40
150CPL	6141627	E940H	EC30	30088700958228	1½"	1-1/2-CONDUIT-SCH-40-CPLG	30
200CPL	6141628	E940J	EC35	30088700958235	2"	2-IN-CONDUIT-SCH-40-CPLG	40
250CPL	6141629	E940K	EC40	30088700567345	2½"	2-1/2-CONDUIT-SCH-40-CPLG	20
300CPL	6141630	E940L	EC45	30088700569516	3"	3-IN-CONDUIT-SCH-40-CPLG	40
350CPL	6141631	E940M	EC50	30088700061096	3½"	3-1/2-CONDUIT-SCH-40-CPLG	30
400CPL	6141632	E940N	EC55	30088700547361	4"	4-IN-CONDUIT-SCH-40-CPLG	20
500CPL	6141633	E940P	EC60	30088700547378	5"	5-IN-CONDUIT-SCH-40-CPLG	10
600CPL	6141634	E940R	EC65	30088700547385	6"	6-IN-CONDUIT-SCH-40-CPLG	8
800CPL	6141635D	N/A	N/A	30088700035950	8"	8-IN-CONDUIT-SCH-40-CPLG	1
FEMALE ADAPTERS							
050FA	5140043	E942D	FA10	30088700958327	½"	1/2-FEMALE-SCH-40-ADPT	200
075FA	5140044	E942E	FA15	30088700958334	¾"	3/4-FEMALE-SCH-40-ADPT	125
100FA	5140045	E942F	FA20	30088700958341	1"	1-IN-FEMALE-SCH-40-ADPT	70
125FA	5140046	E942G	FA25	30088700958358	1¼"	1-1/4-FEMALE-SCH-40-ADPT	40
150FA	5140047	E942H	FA30	30088700958365	1½"	1-1/2-FEMALE-SCH-40-ADPT	30
200FA	5140048	E942J	FA35	30088700958372	2"	2-IN-FEMALE-SCH-40-ADPT	40
250FA	5140049	E942K	FA40	30088700567512	2½"	2-1/2-FEMALE-SCH-40-ADPT	20
300FA	5140050	E942L	FA45	30088700527738	3"	3-IN-FEMALE-SCH-40-ADPT	40
350FA	5140051	E942M	FA50	30088700527745	3½"	3-1/2-FEMALE-SCH-40-ADPT	30
400FA	5140052	E942N	FA55	30088700527752	4"	4-IN-FEMALE-SCH-40-ADPT	20
500FA	5140053	E942P	FA60	30088700527769	5"	5-IN-FEMALE-SCH-40-ADPT	10
600FA	5140054	E942R	FA65	30088700527776	6"	6-IN-FEMALE-SCH-40-ADPT	8
800FA	5140055D	N/A	N/A	30088700036339	8"	8-IN-FEMALE-SCH-40-ADPT	2
TERMINAL ADAPTERS							
050MA	5140103	E943D	TA10	30088700958259	½"	1/2-SCH-40-TERMINAL-ADPT	200
075MA	5140104	E943E	TA15	30088700958266	¾"	3/4-SCH-40-TERMINAL-ADPT	125
100MA	5140105	E943F	TA20	30088700958273	1"	1-IN-SCH-40-TERMINAL-ADPT	70
125MA	5140106	E943G	TA25	30088700958297	1¼"	1-1/4-SCH-40-TERMINAL-ADPT	40
150MA	5140107	E943H	TA30	30088700958303	1½"	1-1/2-SCH-40-TERMINAL-ADPT	30
200MA	5140108	E943J	TA35	30088700958310	2"	2-IN-SCH-40-TERMINAL-ADPT	40
250MA	5140109	E943K	TA40	30088700567420	2½"	2-1/2-SCH-40-TERMINAL-ADPT	20
300MA	5140110	E943L	TA45	30088700568649	3"	3-IN-SCH-40-TERMINAL-ADPT	40
350MA	5140111	E943M	TA50	30088700527790	3½"	3-1/2-SCH-40-TERMINAL-ADPT	30
400MA	5140112	E943N	TA55	30088700527806	4"	4-IN-SCH-40-TERMINAL-ADPT	20
500MA	5140113	E943P	TA60	30088700527813	5"	5-IN-SCH-40-TERMINAL-ADPT	10
600MA	5140114	E943R	TA65	30088700527820	6"	6-IN-SCH-40-TERMINAL-ADPT	8
800MA	5140115D	N/A	N/A	30088700036230	8"	8-IN-SCH-40-TERMINAL-ADPT	2
SCHEDULE 40 STANDARD RADIUS ELBOWS							
90° ELBOWS PLAIN END							
05090ELB	5133823	UA9AD	N/A	30088700958389	½"	1/2-90D-ELL	50
07590ELB	5133824	UA9AE	N/A	30088700958396	¾"	3/4-90D-SCH-40-ELL	35
10090ELB	5133825	UA9AF	N/A	30088700958402	1"	1-IN-90D-SCH-40-ELL	20
12590ELB	5133826	UA9AG	N/A	30088700958419	1¼"	1-1/4-90D-SCH-40-ELL	30
15090ELB	5133827	UA9AH	N/A	30088700958426	1½"	1-1/2-90D-SCH-40-ELL	30
20090ELB	5133828	UA9AJ	N/A	30088700958433	2"	2-IN-90D-SCH-40-ELL	15
25090ELB	5133829	UA9AK	N/A	30088700568199	2½"	2-1/2-90D-SCH-40-ELL	18
30090ELB	5133830	UA9AL	N/A	30088700568526	3"	3-IN-90D-SCH-40-ELL	14
35090ELB	5133831	UA9AM	N/A	30088700518835	3½"	3-1/2-90D-SCH-40-ELL	12
40090ELB	5133832	UA9AN	N/A	30088700518842	4"	4-IN-90D-SCH-40-ELL	10
50090ELB	5133835	UA9AP	N/A	30088700518866	5"	5-IN-90D-SCH-40-ELL	30
60090ELB	5133834	UA9AR	N/A	30088700518859	6"	6-IN-90D-SCH-40-ELL	25



Comparisons relate to function only. Items may not be identical. While information provided has been carefully prepared, we do not assume responsibility for errors.