



JAR



**Phillips Bugle Head Drywall Screw Coarse Thread Phosphate Finish in Jar**

CAT. NO.	SIZE	U/M	STD. BOX	STD. CTN.	WT./UM
005051J	6 x 1"	C	100	3000	0.35
005054J	6 x 1-5/8"	C	100	3000	0.50
005055J	6 x 2"	C	100	1000	0.605



JAR



**Framing Screw Pan Phillips Sharp Point Phosphate Finish in Jar**

CAT. NO.	SIZE	U/M	STD. BOX	STD. CTN.	WT./UM
005185J	6 x 7/16"	C	100	3000	0.30
005190J	6 x 7/16"	C	1000	10,000	0.30



JAR



**Framing Screw Pan Phillips Self Drill Phosphate Finish in Jar**

CAT. NO.	SIZE	U/M	STD. BOX	STD. CTN.	WT./UM
005187J	6 x 7/16"	C	100	3000	0.35
005190J	6 x 7/16"	C	1000	10000	0.35



JAR



**Zinc Tapping Screw Indent Hex Washer Head Slotted in Jar**

CAT. NO.	SIZE	U/M	STD. BOX	STD. CTN.	WT./UM
060006J	#6 X 1-1/4" A	C	100	3000	0.50
060007J	#6 X 3/8" AB	C	100	3000	0.30
060008J	#6 X 1/2" AB	C	100	3000	0.30
060009J	#6 X 3/4" AB	C	100	3000	0.40
060010J	#6 X 1" A	C	100	3000	0.45
060011J	#6 X 1-1/2" A	C	100	3000	0.60
060012J	#8 X 3/8" AB	C	100	3000	0.35
060013J	#8 X 1/2" AB	C	100	3000	0.40
060014J	#8 X 5/8" AB	C	100	3000	0.45
060015J	#8 X 3/4" AB	C	100	3000	0.45
060016J	#8 X 1" A	C	100	3000	0.55
060017J	#8 X 1-1/4" A	C	100	3000	0.65
060018J	#8 X 1-1/2" A	C	100	3000	0.75
060019J	#8 X 2" A	C	100	1000	1.00
060020J	#8 X 2-1/2" A	C	100	1000	1.15
060021J	#8 X 3" A	C	100	1000	1.40
060022J	#10 X 3/8" AB	C	100	3000	0.45
060023J	#10 X 1/2" AB	C	100	3000	0.50
060024J	#10 X 5/8" AB	C	100	3000	0.55
060025J	#10 X 3/4" AB	C	100	3000	0.65
060026J	#10 X 1" A	C	100	3000	0.75

CAT. NO.	SIZE	U/M	STD. BOX	STD. CTN.	WT./UM
060027J	#10 X 1-1/4" A	C	100	2000	0.95
060028J	#10 X 1-1/2" A	C	100	2000	1.00
060029J	#10 X 2" A	C	100	1000	1.30
060030J	#10 X 2-1/2" A	C	100	1000	1.55
060031J	#10 X 3" A	C	100	600	1.90
060032J	#12 X 1/2" AB	C	100	3000	0.70
060033J	#12 X 3/4" AB	C	100	2000	0.95
060034J	#12 X 1" A	C	100	2000	0.98
060035J	#12 X 1-1/4" A	C	100	2000	1.15
060036J	#12 X 1-1/2" A	C	100	2000	1.35
060037J	#12 X 2" A	C	100	1000	1.70
060038J	#12 X 2-1/2" A	C	100	1000	2.05
060039J	#12 X 3" A	C	100	1000	2.35
060040J	#14 X 3/4" AB	C	100	2000	1.30
060041J	#14 X 1" A	C	100	2000	1.45
060042J	#14 X 1-1/4" A	C	100	1000	1.70
060043J	#14 X 1-1/2" A	C	100	1000	1.95
060044J	#14 X 2" A	C	100	1000	2.40
060045J	#14 X 2-1/2" A	C	100	1000	2.85
060046J	#14 X 3" A	C	100	600	3.40



JAR



**Zinc Tapping Screw Indent Hex Washer Head Slot Zip Point in Jar**

CAT. NO.	SIZE	U/M	STD. BOX	STD. CTN.	WT./UM
061017J	#7 X 1/2"	C	100	3000	0.31
061031J	#8 X 1/2"	C	100	3000	0.31
061032J	#8 X 1/2"	C	1000	10000	0.31
061033J	#8 X 3/4"	C	100	3000	0.42
061034J	#8 X 3/4"	C	1000	10000	0.42
061035J	#8 X 1"	C	100	3000	0.51
061036J	#8 X 1"	C	1000	10000	0.51



JAR



**Zinc Tapping Screw Pan Combo (Slot/Phil) in Jar**

CAT. NO.	SIZE	U/M	STD. BOX	STD. CTN.	WT./UM
061102J	#6 X 3/8" AB	C	100	3000	0.25
061103J	#6 X 1/2" AB	C	100	3000	0.25
061105J	#6 X 3/4" AB	C	100	3000	0.35
061106J	#6 X 1" A	C	100	3000	0.40
061107J	#6 X 1-1/4" A	C	100	3000	0.45
061108J	#6 X 1-1/2" A	C	100	3000	0.55
061109J	#6 X 2" A	C	100	2000	0.65
061110J	#8 X 3/8" AB	C	100	3000	0.35
061111J	#8 X 1/2" AB	C	100	3000	0.40
061113J	#8 X 3/4" AB	C	100	3000	0.45
061114J	#8 X 1" A	C	100	3000	0.55
061115J	#8 X 1-1/4" A	C	100	3000	0.65
061116J	#8 X 1-1/2" A	C	100	2000	0.80
061118J	#8 X 2" A	C	100	1000	1.00
061119J	#8 X 2-1/2" A	C	100	1000	1.15
061120J	#8 X 3" A	C	100	1000	1.40
061122J	#10 X 1/2" AB	C	100	3000	0.55
061124J	#10 X 3/4" AB	C	100	3000	0.65
061125J	#10 X 1" A	C	100	3000	0.75
061126J	#10 X 1-1/4" A	C	100	2000	0.85
061127J	#10 X 1-1/2" A	C	100	2000	1.00
061129J	#10 X 2" A	C	100	1000	1.25
061130J	#10 X 2-1/2" A	C	100	1000	1.55