

# INSPIRE



P4635-09

Freshen traditional forms with flowing lines found in the Inspire collection. Overarching metal arms are gracious in size and contribute to an updated traditional feel, while Inspire's off white linen drum shades enhance a back-to-basic design.

#### FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

**PAIR WITH**  
Drum Shade  
Tally

**ALSO AVAILABLE IN**  
Bath & Vanity  
Close-to-Ceiling



P4739-09

P4632-09  
*shown with  
included shades*

**ONE-LIGHT FOYER PENDANT**  
**P3799-09** Brushed Nickel  
14-3/4" dia., 20-1/4" ht.,  
Overall ht. w/chain 96"; wire 10'.  
One medium base lamp,  
100w max.

**THREE-LIGHT INVERTED PENDANT**  
**P3931-09** Brushed Nickel  
White acrylic diffuser.  
19" dia., 21-1/2" ht.  
Overall ht. w/chain 96"; wire 10'.  
Three medium base lamps,  
each 100w max.

P3799-09

**THREE-LIGHT CHANDELIER**  
**P4632-09** Brushed Nickel  
17" dia., 18" ht.  
Overall ht. w/chain 92-1/4"; wire 10'.  
Three candelabra base lamps,  
each 60w max.

**FIVE-LIGHT CHANDELIER**  
**P4635-09** Brushed Nickel  
23" dia., 20" ht.  
Overall ht. w/chain 94"; wire 10'.  
Five candelabra base lamps,  
each 60w max.

P4638-09

P3931-09

**NINE-LIGHT CHANDELIER**  
**P4638-09** Brushed Nickel  
Two-tier.  
29-3/8" dia., 31" ht.  
Overall ht. w/chain 105"; wire 12'.  
Nine candelabra base lamps,  
each 60w max.

**FIFTEEN-LIGHT CHANDELIER**  
**P4650-09** Brushed Nickel  
Three-tier.  
39-1/2" dia., 40-1/4" ht.  
Overall ht. w/chain 163-1/4"; wire 12'.  
Fifteen candelabra base lamps,  
each 60w max.

P4650-09

P5065-09

**SIX-LIGHT CHANDELIER**  
**P4739-09** Brushed Nickel  
30" dia., 22" ht.  
Overall ht. w/chain 97"; wire 10'.  
Six candelabra base lamps,  
each 60w max.

**MINI-PENDANT**  
**P5065-09** Brushed Nickel  
6-1/2" dia., 6-1/4" ht.  
Overall ht. w/chain or stem 93"; wire 10'.  
One medium base lamp,  
100w max.

**SCONCE**  
**P7026-30** Off-White  
6" W., 9" ht.  
Extends 3-7/8". H/CTR 4-1/2".  
One 13w max., GU24 lamp.



P7026-30



Shown: P4638-20 chandelier (Image: Toll Brothers)



P4632-20  
shown without  
included shades



P4632-20  
shown with  
included shades



P4739-20



P4635-20



P4638-20



P3799-20



P4650-20



P3931-20



P5065-20

P7026-30

# INSPIRE

## ONE-LIGHT FOYER PENDANT

**P3799-20** Antique Bronze  
14-3/4" dia., 20-1/4" ht.,  
Overall ht. w/chain 96"; wire 10'.  
One medium base lamp,  
100w max.

## THREE-LIGHT INVERTED PENDANT

**P3931-20** Antique Bronze  
White acrylic diffuser.  
19" dia., 21-1/2" ht.  
Overall ht. w/chain 96"; wire 10'.  
Three medium base lamps,  
each 100w max.

## THREE-LIGHT CHANDELIER

**P4632-20** Antique Bronze  
17" dia., 18" ht.  
Overall ht. w/chain 92-1/4"; wire 10'.  
Three candelabra base lamps,  
each 60w max.

## FIVE-LIGHT CHANDELIER

**P4635-20** Antique Bronze  
23" dia., 20" ht.  
Overall ht. w/chain 94"; wire 10'.  
Five candelabra base lamps,  
each 60w max.

## NINE-LIGHT CHANDELIER

**P4638-20** Antique Bronze  
Two-tier.  
29-3/8" dia., 31" ht.  
Overall ht. w/chain 105"; wire 12'.  
Nine candelabra base lamps,  
each 60w max.

## FIFTEEN-LIGHT CHANDELIER

**P4650-20** Antique Bronze  
Three-tier.  
39-1/2" dia., 40-1/4" ht.  
Overall ht. w/chain 163-1/4"; wire 12'.  
Fifteen candelabra base lamps,  
each 60w max.

## SIX-LIGHT CHANDELIER

**P4739-20** Antique Bronze  
30" dia., 22" ht.  
Overall ht. w/chain 97"; wire 10'.  
Six candelabra base lamps,  
each 60w max.

## MINI-PENDANT

**P5065-20** Antique Bronze  
6-1/2" dia., 6-1/4" ht.  
Overall ht. w/chain or stem 93"; wire 10'.  
One medium base lamp,  
100w max.

## SCONCE

**P7026-30** Off-White  
6" W., 9" ht.  
Extends 3-7/8". H/CTR 4-1/2".  
One 13w max., GU24 lamp.



# INSPIRE



Updated traditional inspiration with gracious, flowing oval arms and etched glass shades.

## FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

## ALSO AVAILABLE IN

Fixture Collections  
Close-to-Ceiling

### ONE-LIGHT BATH

**P2018-09** Brushed Nickel  
4-5/8" W., 7-1/2" ht.  
Extends 7-3/8". H/CTR 3-3/4".  
One medium base lamp,  
100w max.

### TWO-LIGHT BATH

**P2019-09** Brushed Nickel  
15" W., 8-1/2" ht.  
Extends 6-7/8". H/CTR 6-1/8".  
Two medium base lamps,  
each 100w max.

### THREE-LIGHT BATH

**P2020-09** Brushed Nickel  
22-3/8" W., 8-1/4" ht.  
Extends 6-7/8". H/CTR 5-1/2".  
Three medium base lamps,  
each 100w max.

### FOUR-LIGHT BATH

**P2021-09** Brushed Nickel  
31-3/8" W., 8-1/2" ht.  
Extends 6-7/8". H/CTR 6-1/8".  
Four medium base lamps,  
each 100w max.



P2018-09



P2019-09



P2020-09



P2021-09



P2018-20



P2019-20



P2020-20



P2021-20



P2018-15



P2019-15



P2020-15



P2021-15



P2018-20  
*mounted down*



P2019-20  
*mounted down*



P2020-20  
*mounted down*



P2021-20  
*mounted down*

### ONE-LIGHT BATH

**P2018-15** Polished Chrome  
**P2018-20** Antique Bronze  
4-5/8" W., 7-1/2" ht.  
Extends 7-3/8". H/CTR 3-3/4".  
One medium base lamp,  
100w max.

### TWO-LIGHT BATH

**P2019-15** Polished Chrome  
**P2019-20** Antique Bronze  
15" W., 8-1/2" ht.  
Extends 6-7/8". H/CTR 6-1/8".  
Two medium base lamps,  
each 100w max.

### THREE-LIGHT BATH

**P2020-15** Polished Chrome  
**P2020-20** Antique Bronze  
22-3/8" W., 8-1/4" ht.  
Extends 6-7/8". H/CTR 5-1/2".  
Three medium base lamps,  
each 100w max.

### FOUR-LIGHT BATH

**P2021-15** Polished Chrome  
**P2021-20** Antique Bronze  
31-3/8" W., 8-1/2" ht.  
Extends 6-7/8". H/CTR 6-1/8".  
Four medium base lamps,  
each 100w max.

# INSPIRE

---

Off-white linen shade with white acrylic diffuser.

## TWO-LIGHT SEMI-FLUSH

**P3712-09** Brushed Nickel

**P3712-20** Antique Bronze

13" dia., 10-1/8" ht.

Two medium base lamps, each 75w max.

## TWO-LIGHT FLUSH MOUNT

**P3713-09** Brushed Nickel

**P3713-20** Antique Bronze

13" dia., 5-1/2" ht.

Two medium base lamps, each 60w max.

## TWO-LIGHT CFL SEMI-FLUSH

**P3939-09** Brushed Nickel

**P3939-20** Antique Bronze

White acrylic diffuser.

13" dia., 10-1/2" ht.

Two GU24 CFL lamps, each 26w max.



P3712-20



P3712-09



P3712-20



P3712-09



P3939-20



P3939-09

# INSPIRE LED

---

Off-white linen shade with diffuser.

## LED SEMI-FLUSH MOUNT

**P3683-0930K9** Brushed Nickel

**P3683-2030K9** Antique Bronze

13" dia., 10-5/8" ht.

One 3000K 17w LED  
module included.

1452 source lumens, 90 CRI.



P3683-2030K9



P3683-0930K9

## LED FLUSH MOUNT

**P3696-0930K9** Brushed Nickel

**P3696-2030K9** Antique Bronze

13" dia., 6" ht.

One 3000K 17w LED  
module included.

1452 source lumens, 90 CRI.



P3696-2030K9



P3696-0930K9

