

(UL) THERMOSTAT CABLE

PVC Rated -18 AWG
UL Listed Type CL-2/MPR



CONSTRUCTION	
Conductor	- Solid Bare Copper
Insulation	- Color coded PVC
Jacket	- Sunlight resistant PVC - Stock color white, but also available in brown

COLOR CODE CHART	
Cond. #	Color
1	Red
2	White
3	Green
4	Blue
5	Yellow
6	Tan
7	Orange
8	Black
9	Pink
10	Brown

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'	Standard Box Quantities
D201802	18	2	.005"	.015"	.140"	19	4 x 500'
D201803	18	3	.005"	.015"	.180"	27	4 x 500'
D201804	18	4	.005"	.015"	.195"	35	4 x 250'
D201805	18	5	.005"	.015"	.215"	40	4 x 250'
D201806	18	6	.005"	.015"	.233"	48	4 x 250'
D201808	18	8	.005"	.015"	.252"	60	4 x 250'
D201810	18	10	.005"	.015"	.298"	76	4 x 250'

* Also available in Bulk Lengths.

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.