

LED ROPE LIGHT

- Cost effective lighting for a variety of applications
- Vibrant, long lasting colors that grab attention
- Consumes 85% less energy and lasts up to four times longer than incandescent rope light
- Produces virtually no heat for maximum safety
- Each reel includes one molded power cord, five connector kits and 50 mounting clips
- UL Listed for indoor or outdoor use (no longer UL listed if cut)



LED



PART NUMBER	COLOR
1/2" Rope light - 150 ft - 0.8W per ft	
ULRL-LED-AM-150	AMBER
ULRL-LED-BL-150	BLUE
ULRL-LED-GR-150	GREEN
ULRL-LED-RE-150	RED
ULRL-LED-WH-150	BRIGHT WHITE
ULRL-LED-WW-150	WARM WHITE
ULRL-LED-YE-150	YELLOW
3/8" Rope light - 150 ft - 0.8W per ft	
LED-MRL-AM-150	AMBER
LED-MRL-BL-150	BLUE
LED-MRL-GR-150	GREEN
LED-MRL-RED-150	RED
LED-MRL-WH-150	BRIGHT WHITE
LED-MRL-WW-150	WARM WHITE
LED-MRL-YE-150	YELLOW



POWER ACCESSORIES

PART NUMBER	DESCRIPTION
1/2" Rope Light Accessories	
RL-LED-CONKIT-1.6AMP	Power connector kit with 120V AC power cord, power connector, end cap
RL-PWR	Non-UL power connector
RL-INV SPL	Invisible splice connector for connecting sections of rope light; use with RL-ST-3
RL-ST-3	Clear shrink tube for use with invisible splice connections; 3" in length, sold in bags of 10
RL-TRACK-4	4ft long clear mounting track for straight line installations, with UV stabilizer for outdoor use
RL-CLIP/SCREW	Clear "U" shaped mounting clip to securely hold rope light in place. Includes one mounting screw
3/8" Rope Light Accessories	
MRL-LED-CONKIT-1.6AMP	Power connector kit with 120V AC power cord, power connector, end cap
MRL-LED-PWR	Non-UL power connector
MRL-LED-INV SPL	Invisible splice connector for connecting sections of rope light; use with MRL-ST-3
MRL-ST-3	Clear shrink tube for use with invisible splice connections; 3" in length, sold in bags of 10
MRL-TRACK-4	4ft long clear mounting track for straight line installations,with UV stabilizer for outdoor use
MRL-CLIP/SCREW	Clear "U" shaped mounting clip to securely hold rope light in place. Includes one mounting screw



Power Connector Kit
(RL-LED-CONKIT-1.6AMP)
(MRL-LED-CONKIT-1.6AMP)



Power Connector
(RL-PWR)
(MRL-LED-PWR)



Splice Connector
(RL-INV SPL)
(MRL-LED-INV SPL)



Shrink Tube
(RL-ST-3)
(MRL-ST-3)



Mounting Track
(RL-TRACK-4)
(MRL-TRACK-4)



Mounting Clip
(RL-CLIP/SCREW)
(MRL-CLIP/SCREW)

TECHNICAL SPECIFICATIONS

Voltage	120V, 60Hz AC operation (1.6A inverter on power cord converts AC to DC)
Construction	Heat resistant clear PVC housing with LEDs every 1", vertical mount
Cuttability	AM, RE, YE = 60", BL, GR, WH and WW = 36" (no longer UL Listed if cut)
Wattage	LED 0.8 watt per ft
Power cord	5 ft length with two blade polarized plug, white
Maximum run	150 ft length
Rated life	60,000 hours average rated life