




CATALOG NUMBER: See table below
DESCRIPTION: "T"-slot extension cord
APPROVALS: UL/CUL Listed Outdoor Use Cord Set

CONSTRUCTION PARAMETERS:

Cable type: 10/3 SJTOW
 Cable jacket material: PVC, low durometer, yellow
 Cord rating: Hard Usage per the National Electrical Code
 Cable legend type: Indent print



Note: Plug style may vary

Attachment plug configuration: NEMA 5-20P
 Cord connector configuration: NEMA 5-20R
 Plug material: PVC, black
 Connector material: Clear PVC, with neon power indicator lamp

ELECTRICAL AND ENVIRONMENTAL PROPERTIES:

Cable temperature rating: -40 to +60 °C
 Nominal operating voltage: 125 VAC
 Maximum operating current: 20 A

Catalog no.	Length	Case qty	UPC
26188802	50 ft	2	0 29892 33514 4
26198802	100 ft	2	0 29892 33515 1

This product complies with European Directive 2011/65/EU (RoHS-2),

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part.

We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is the proprietary intellectual property of Southwire Company LLC. Any information contained herein shall not be disclosed to any party without the written consent of Southwire Company LLC.