

MIGHTYLITE

LED SECURITY FLOODLIGHT



High performance, reliable, British-designed LED floodlights which deliver up to 4200 lumens of light from a compact and stylish fitting.

Mightylite floodlights are, for their size, very powerful high quality LED floodlights. They are ideal for both domestic and commercial applications.

The Mightylite fits easily under eaves, using the waterproof universal mounting bracket which attaches the unit straight to the wall.

The floodlights are supplied with a vandal-proof black polycarbonate fascia on a black aluminium body, and feature a clear lens for improved light output.

✓ **Industry-leading performance**

Generates up to 84 Lumens per Watt

✓ **Powered by British designed driver**

Combined with the latest high powered Epistar LEDs to deliver unmatched levels of light and exceptional reliability

✓ **Inter-linkable with Mightylite with PIR**

Can work as an independent floodlight, or be linked to and activated by a Mightylite with PIR for full perimeter security

✓ **Weatherproof**

IP65 rating and works in temperatures from -22°F to +176°F

✓ **Fully certified**

ETL, RoHS, LVD approvals and ERP compliant

SPECIFICATIONS

Model No:	MITY22BLK	MITY64BLK	MITY82BLK
Lumens:	1200Lm	2300Lm	4200Lm
Wattage:	16W	28W	50W
Power Factor:	>0.9	>0.9	>0.9
Voltage:	110V AC	110V AC	110V AC
Color Temp:	5400K	5400K	5400K
Efficiency:	<80%	<80%	<80%
LED Array:	24 LEDs	24 LEDs	42 LEDs
Lens:	Clear	Clear	Clear
Operating Temp:	-22°F to +176°F	-22°F to +176°F	-22°F to +176°F
IP Rating:	IP65	IP65	IP65
Product Size:	4.3"(h) x 6.3"(w) x 2"(d)	4.3"(h) x 6.3"(w) x 2"(d)	4.3"(h) x 6.3"(w) x 4.9"(d)