

MIGHTYLITE

LED SECURITY FLOODLIGHT WITH PIR



High performance, reliable, LED floodlights which deliver up to 3000 lumens of light from a compact and stylish fitting.

Mightylite floodlights are, for their size, very powerful high quality LED floodlights. They are ideal for both domestic and commercial applications.

The Mightylite fits easily under eaves, using the waterproof universal mounting bracket which attaches the unit straight to the wall.

The floodlights are supplied with a vandal-proof white polycarbonate fascia on a black aluminium body, and feature a clear lens for improved light output.

✓ Industry-leading performance

Generates up to 84 Lumens per Watt

✓ Powered by British designed driver

Combined with the latest high powered Epistar LEDs to deliver unmatched levels of light and exceptional reliability

✓ Inter-linkable with Mightylite with PIR

Can work as an independent floodlight, or be linked to and activated by a Mightylite with PIR for full perimeter security

✓ Weatherproof

IP65 rating and works in temperatures from -22°F to +176°F

✓ Fully certified

ETL, RoHS, LVD approvals and ERP compliant

SPECIFICATIONS

Model No:	MITY222WHT	MITY264WHT	MITY276WHT
Lumens:	1200Lm	2300Lm	3000Lm
Wattage:	16W	28W	36W
Power Factor:	>0.9	>0.9	>0.9
Voltage:	110V AC	110V AC	110V AC
Color Temp:	5400K	5400K	5400K
Efficiency:	<80%	<80%	<80%
LED Array:	24 LEDs	24 LEDs	30 LEDs
PIR Range:	26ft - 39ft	26ft - 39ft	26ft - 39ft
PIR Angle:	120°	120°	120°
Activation Time:	5 secs to 15 mins	5 secs to 15 mins	5 secs to 15 mins
Lens:	Clear	Clear	Clear
Operating Temp:	-22°F to +176°F	-22°F to +176°F	-22°F to +176°F
IP Rating:	IP65	IP65	IP65
Product Size:	4.3"(h) x 6.3"(w) x 2"(d)	4.3"(h) x 6.3"(w) x 2"(d)	4.3"(h) x 6.3"(w) x 2"(d)