


GARDIAN PREASSEMBLED

- Roof and gutter de-icing
- Metal/plastic pipes, up to 2-1/2" in diameter
- Wet or Dry areas



- Gardian 120 V
- Plug-in heating cable with 30-inch cold lead
- Braid and jacket
- 6 W/ft @ 40°F; 200 ft max. circuit



- Gardian 240 V
- 30-inch cold lead for hardwiring
- Braid and jacket
- 6 W/ft @ 40°F; 400 ft max. circuit

WINTERGARD

- Metal/plastic pipes, up to 2" in diameter
- Dry areas only



- WinterGard 120 V
- Braid only
- 3 W/ft @ 40°F; 250 ft max. circuit

WINTERGARD PLUS

- Metal/plastic pipes, up to 6" in diameter
- Dry areas only



- WinterGard Plus 120 V
- Braid only
- 6 W/ft @ 40°F; 200 ft max. circuit



- WinterGard Plus 240 V
- Braid only
- 6 W/ft @ 40°F; 400 ft max. circuit

WINTERGARD WET

- Roof and gutter de-icing
- Metal/plastic pipes, up to 6" in diameter
- Wet or Dry areas



- WinterGard Wet 120 V
- Braid and jacket
- 6 W/ft @ 40°F; 200 ft max. circuit



- WinterGard Wet 240 V
- Braid and jacket
- 6 W/ft @ 40°F; 400 ft max. circuit

FROSTEX

- Metal/plastic pipes, up to 2" in diameter
- Dry areas only



- Frostex 120 V
- Braid only
- 3 W/ft @ 50°F; 50 ft max. circuit

IN-PIPE

- Plastic pipes up to 1-1/4" in diameter
- **Mini** 120 V for insulated pipes up to 34 feet length
- **Miser** 120 V for insulated pipes up to 240 feet length
- **Retro** 120 V for uninsulated pipes up to 150 feet length
- **Retro** 240 V for uninsulated pipes up to 250 feet length



- In-Pipe 120 V
- Mini / Miser short lengths are stainless steel
- Miser long lengths are copper sheathed MI
- Miser has built-in ground-fault protection
- 4 W/ft Mini & Miser; 8 W/ft Retro



- In-Pipe Retro 240 V
- Copper sheathed MI
- Between 160 ft and 250 ft
- 8 W/ft

FREEZGARD

- Crankcase heater
- Fits compressors up to 40 inches in circumference



- FreezGard 120 V
- Braid and jacket



- FreezGard 208-277 V
- Braid and jacket



GARDIAN PREASSEMBLED

- Heating cable options ➡
- Accessories:
 - » For pipes: H903 application tape
 - » For roofs: H913/H914 roof clips; H915 downspout hanger
- Control options:
 - » TC-3 thermostatically controlled outlet

GARDIAN 120 V

Description	Catalog #
6' Length	W51-6P
12' Length	W51-12P
18' Length	W51-18P
24' Length	W51-24P
50' Length	W51-50P
75' Length	W51-75P
100' Length	W51-100P

GARDIAN 240 V

Description	Catalog #
6' Length	W52-6L
12' Length	W52-12L
18' Length	W52-18L
24' Length	W52-24L

WINTERGARD

- Heating cable options ➡
- Accessories:
 - » For pipes: H900 hardwire or H908 plug-in power connection kit; H903 application tape; H910 Splice/Tee kit
- Control options:
 - » AMC-F5, AMC-1A, EC-TS, SST-2

WINTERGARD 120 V

Description	Catalog #
100' TruckPak*	H311100
250' Reel	H311250

*WinterGard TruckPaks contains 100 feet of heating cable, two H900 Hardwire Power Connection Kits, one H910 Splice or Tee Kit, and one H903 roll of Application Tape.

WINTERGARD PLUS

- Heating cable options ➡
- Accessories:
 - » For pipes: H900 hardwire or H908 plug-in power connection kit; H903 application tape; H910 Splice/Tee kit
- Control options:
 - » AMC-F5, AMC-1A, EC-TS, SST-2

WINTERGARD PLUS 120 V

Description	Catalog #
50' Box	H611050
100' TruckPak*	H611100
250' Reel	H611250

WINTERGARD PLUS 240 V

Description	Catalog #
50' Box	H621050
100' TruckPak*	H621100
250' Reel	H621250

WINTERGARD WET

- Heating cable options ➡
- Accessories:
 - » For pipes: H900 hardwire or H908 plug-in power connection kit; H903 application tape; H910 Splice/Tee kit
 - » For roofs: H900 hardwire or H908 plug-in power connection kit; H913/H914 roof clips; H915 downspout hanger; H910 Splice/Tee kit
- Control options:
 - » AMC-F5, AMC-1A, EC-TS, SST-2
 - » PD-Pro, GF-Pro, CIT-1, GIT-1, LCD-8

WINTERGARD WET 120 V

Description	Catalog #
50' Box	H612050
100' TruckPak*	H612100
250' Reel	H612250
500' Reel	H612500
1000' Reel	H6121000

WINTERGARD WET 240 V

Description	Catalog #
50' Box	H622050
100' TruckPak*	H622100
250' Reel	H622250
500' Reel	H622500
1000' Reel	H6221000

FROSTEX

- Heating cable options ➡
- Accessories:
 - » 9800 FlexFit plug kit; 9610 Application tape
- Control options:
 - » TC-3 thermostatically controlled outlet

FROSTEX 120 V

Description	Catalog #
50' TruckPak**	5050
100' Reel	2102
250' Reel	2250
500' Reel	2502

**Frostex TruckPaks contains 50 feet of Frostex Heating Cable, 2 each 9800 FlexFit Plug Kits, and 1 each 9610 Application Tape.

IN-PIPE

- Heating cable options ➡
- Control options:
 - » Built-in controller

IN-PIPE 120 V


Description	Catalog #
Mini 14' - 34'	see price list for 6 sizes
Miser 14' - 240'	see price list for 27 sizes
Retro 40' - 150'	see price list for 12 sizes

IN-PIPE 240 V

Description	Catalog #
Retro 160' - 250'	see price list for 10 sizes

FREEZGARD

- Crankcase heaters ➡



FREEZGARD 120 V

Description	Catalog #
120 V Heater	CCH-1C

FREEZGARD 240 V

Description	Catalog #
240 V Heater	CCH-2C