

TO INSTALL:

WARNING: IF YOU ARE NOT SURE ABOUT ANY PART OF THESE INSTRUCTIONS, CONSULT A QUALIFIED ELECTRICIAN.

FOR SEPARATE FEED CONVERSION ONLY: Our outlet is provided with a break-off fin located between the two brass terminal screws. If you want to have the top outlet and the bottom outlet controlled by two different hot wires (two circuits), remove the break-off fin before wiring. With needlenose pliers, bend fin back and forth until it breaks off.

1. **WARNING:** TO AVOID FIRE, SHOCK, OR DEATH; **TURN OFF POWER AT CIRCUIT BREAKER OR FUSE AND TEST THAT THE POWER IS OFF BEFORE WIRING!**
2. Remove insulation per strip gauge on device [about 5/8" (1.6 cm)].
3. Connect wires per **WIRING DIAGRAM** as follows: Loop wires clockwise 3/4 turn around terminal screws. **BLACK (hot) wire to BRASS screw, WHITE (neutral) wire to SILVER screw, GREEN or BARE (ground) wire to GREEN screw.** Firmly tighten screws over wire loops. Terminal screws accept up to #12 AWG copper or copper clad wire.
4. Mount device using long mounting screws. Attach wallplate (not included).
5. Restore power at circuit breaker or fuse. **Installation is complete.**

