

**Dover Collection**  
**Dover 3 Bulb Semi Flush Ceiling Light - NI**  
 3623NI (Brushed Nickel)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_



**Ordering Information**

Product ID	3623NI
Finish	Brushed Nickel
Available Finishes	NI, OZ, TZ
Collection	Dover Collection

**Dimensions**

Base Backplate	5.00 DIA
Weight	5.00 LBS

**Specifications**

Material	Steel
Glass Description	Etched Seeded

**Electrical**

Voltage	120V
---------	------

**Qualifications**

Safety Rated	Dry
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

**Primary Lamping**

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	3
Max or Nominal Watt	60W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

**Dimensions**

Height	14.00"
Width	15.25"

**Alternate Lamps**

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	13-15W		