



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BR1224B100R**

**UPC:** 786676443951

**Dimensions:** 3.88 IN \* 14.31 IN \* 39 IN (L \* W \* H)

**Notes:** No Data

**Warranty:** 10 year

### Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 100A
- **Box Size:** B2r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Number Of Circuits:** 24
- **Number Of Spaces:** 12
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-1/0 AWG Cu/Al at 60°C or 75°C
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR1224B100R](#)

**Certifications:** No Data

**Product compliance:** No Data



