

Rigid Non-Metallic Conduit Bodies & Covers
T&B Catalog Number:



UPC Number: E986K
Status: 03448106548
Description: Active

Type LB Conduit Body, Volume 210 Cubic Inches, Size 2-1/2 Inches, Length 13-1/4 Inches, Width 4-11/32 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit

Features

- Textured lids
- Foam-in-place gasket

Application

For use with Rigid Conduit

General

Trade Size (inches)	2-1/2
Material	Non-Metallic
Volume (cu.in.)	210
Conduit Body Shape	LB

Dimension Information


C (inches)	1 5/8
H (inches)	3 3/4
L1 (inches)	14 7/8
L2 (inches)	13 1/4
L3 (inches)	11 31/32
Q (inches)	4 11/32
W (inches)	4 5/8

Packaging

Package in Units	4
T&B Sold in UOM	Each
T&B Weight Per UOM	3.33 lbs. Each

Application Support

Rigid Non-metallic Conduit Bodies	Available on Website
Specifications & Applications	Available on Website



For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com