



Select a Language

SEARCH

Supplier Center Distributor Center

BROWSE PRODUCTS

Category: [-- Select --] Browse by Brand: [--Select--]

PRODUCTS

Bending

Cable Termination > DIE CABLE CRIMPERS > Battery-6 Ton > CRIMP TOOL, BAT 6T 120V CHRGR

Bolt Cutters

CRIMP TOOL, BAT 6T 120V CHRGR

Cable Termination

CATV/Broadband Instruments

Images Video

Connectors

Electric Test Instruments



Fasteners

Fiber Connections

Fiber Optic Instruments

Fishing

Hydraulic Tools

Knockout Sets

Material Handling

Network Instruments

Pipe Tools

Power Tool Accessories

Professional Hand Tools

Pulling

Safety Products

Storage

Telco Instruments

VDV Instruments

VDV Termination

VDV Tools

Wire Termination

SAVE PRODUCT TO PDF

Related Products



User Reviews

(No Reviews Yet.)

Cat No: EK628L11 UPC No: 783310521020

Request Product Info or Demo ▶

Where to Buy ▶

Description Specifications Documents Reviews

- Accessory : K22S1GL UPC 03078 Die Kit for 8 AWG-600 kCMIL Copper Connectors (Includes All Copper Die Sets Listed Below And Carrying Case), KD06AL UPC 01631 Die Kit for 8 AWG-350 kCMIL Aluminum Connectors (Includes All Aluminum Die Sets Listed Below And Carrying Case)
- Battery : 18 V, 1.5 AMP-HR Lithium-Ion
- Battery Charge Time : 30 Minutes
- Crimp Cycle Time : 6 Seconds
- Crimping Capacity : 8 AWG - 600 KCMIL Copper Color Coded Connectors, 8 AWG - 350 KCMIL Aluminum Color Coded Connectors
- Crimping Force : 12000.000 LB (53.000 KN)
- Estimated Cycles per Charge : 150
- Overall Length : 18-1/2 IN (470.000 MM)
- Replacement Part : 25752 UPC 25752 Carrying Case, 52177 UPC 52177 18 V 1.5 AMP-HR Li-Ion Battery, 52178 UPC 52178 120 V Charger, 52179 UPC 52179 12 V Charger, 52130 UPC 52130 230 V Charger
- Rotation : 350°
- Standard : C/US UL Listed
- Type : Battery Powered
- Weight : 6.000 LB (2.700 KG)
- Width : 2-7/8 IN (73.000 MM)

