



NON-RECESSED NICKEL F-CONNECTOR, WHITE

WP3479-WH | [On-Q](#)

FEATURES & BENEFITS

This high quality insert is for use in all Keystone Wall Plates



- Recessed hex nut does not allow for jack rotation
- Contractor packs available in quantities of 50. To order, use part number WP3479-WH-50

SPECIFICATIONS

GENERAL INFO

Color: White
Connection Type: F Connector
Type: Keystone Insert

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPSC: 39121704

DIMENSIONS

Depth (Metric): 3 cm
Depth (US): 1.20"
Length (Metric): 2.2 cm
Length (US): 0.87"
Width (Metric): 1.7 cm
Width (US): 0.67 in

TECHNICAL INFORMATION

Material: High Impact Flame Retardant Plastic
Operating Temperature (Celsius): -55°C to 155°C
Output Impedance: 75 ohm
Product Fits Into: Keystone Cutout
RatedVoltage: 500V Peak Voltage Rating