



## PRODUCT SPECIFICATION

Controlled Document - Engineering Drive

<b>CATALOG NUMBER:</b>	See table below																								
<b>DESCRIPTION:</b>	SJEOOW outdoor use replacement power supply cords																								
<b>APPROVALS:</b>	UL Listed																								
<b>CONSTRUCTION PARAMETERS:</b>																									
Conductors:	See table below																								
Conductor O.D. (nom):	See table below																								
Insulated conductor O.D. (nom):	See table below																								
Insulation material:	TPE																								
Insulation colors:	Black White Green																								
Overall cable O.D. (nom):	See table below																								
Jacket material:	TPE, black																								
Attachment plug configuration:	NEMA 5-15P																								
Plug material:	PVC, black																								
Open end configuration:	3" ROJ, no conductor strip																								
<b>ELECTRICAL PROPERTIES:</b>																									
Cable temperature rating:	-50 to +105 °C																								
Nominal operating voltage:	125 VAC																								
Maximum operating current:	See table below																								
<b>CATALOG NUMBERS:</b>																									
<table border="1"> <thead> <tr> <th>Catalog number</th> <th>Length</th> <th>Conductor</th> <th>Conductor O.D.</th> <th>Insulated conductor O.D.</th> <th>Overall cable O.D.</th> <th>Maximum current</th> </tr> </thead> <tbody> <tr> <td>09855</td> <td>6 ft.</td> <td rowspan="2">16/3, 26x30 bare copper</td> <td rowspan="2">0.059 in.</td> <td rowspan="2">0.120 in.</td> <td rowspan="2">0.330 in.</td> <td rowspan="2">13 A</td> </tr> <tr> <td>09856</td> <td>9 ft.</td> </tr> <tr> <td>09857</td> <td>6 ft.</td> <td rowspan="2">14/3, 41x30 bare copper</td> <td rowspan="2">0.074 in.</td> <td rowspan="2">0.136 in.</td> <td rowspan="2">0.370 in.</td> <td rowspan="2">15 A</td> </tr> <tr> <td>09858</td> <td>9 ft.</td> </tr> </tbody> </table>	Catalog number	Length	Conductor	Conductor O.D.	Insulated conductor O.D.	Overall cable O.D.	Maximum current	09855	6 ft.	16/3, 26x30 bare copper	0.059 in.	0.120 in.	0.330 in.	13 A	09856	9 ft.	09857	6 ft.	14/3, 41x30 bare copper	0.074 in.	0.136 in.	0.370 in.	15 A	09858	9 ft.
Catalog number	Length	Conductor	Conductor O.D.	Insulated conductor O.D.	Overall cable O.D.	Maximum current																			
09855	6 ft.	16/3, 26x30 bare copper	0.059 in.	0.120 in.	0.330 in.	13 A																			
09856	9 ft.																								
09857	6 ft.	14/3, 41x30 bare copper	0.074 in.	0.136 in.	0.370 in.	15 A																			
09858	9 ft.																								

*This product complies with European Directive 2002/95/EC (RoHS)*

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Inc.