



S4481

KX40CL/3M/E12
40 watt; Halogen; T3; Clear; 3000 Average rated Hours; 560 Lumens; Candelabra base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S4481

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S4481	045923044816	40	120	T3	Candelabra	E12	KX40CL/3M/E12
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	2-7/16"	0.38"	CC-8	560	2900	Warm White	3000
Pack	Package Type	Dimmable/Non-Dimmable			RoHS Compliant		
10	Box	Dimmable			Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

