



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
6.50"	6.00"	3.03"
<u>BP Height</u>	<u>BP Width</u>	
6.13"	4.13"	
<u>Hanging Weight</u>		
1.50 lb		

Lamping:

Incandescent MB Incandescent	1,150 Rated Lumens
1.00 100W MB Incandescent	Color Temperature
100 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
2.00 lb	8.46"	8.07"	8.46"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209268616	Yes	

Finish:

Satin Nickel SN

Glass:

Marble MR

Material:

Steel

Certification:

Wet Location
Location

Additional:

MB Incandescent (Not Included)
Lighting Direction: Both