



BURNDY Catalog Number
UPC Number
Description
Status

YAZ292N
 7818102086011
 250 CU-LONG-OPEN-2 NEMA
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

Straight
 5.18
 Skived
 0.52
 Long
 0.16
 1.62
 1.10
 1.75
 1-11/16

Number of Holes

General

2
 Copper Compression Lug, 2 Hole
 w/ Inspection Window, 250 kcmil,
 1/2" Stud, 1-3/4" Stud Hole
 Spacing, Long Barrel, Tin Plated

Product Description

Conductor(s)

Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

N/A
 250 (61) Navy
 250 kcmil

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 1/2
 Yellow
 Y
 16
 Copper

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications

Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175