


[On Line Catalog](#)


BURNDY Catalog Number YA6C2TC38
UPC Number 7818100191600
Description CU HYDENT 6 STR-(2) 3/8
Status Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.22
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.06
B Length (in)	1.12
Pad Width (in)	0.58
E - in	1.00
Strip Length	1-3/16

Number of Holes

General

2
 Copper Compression Lug, 2 Hole
 w/o Inspection Window, 6 AWG,
 3/8" Stud, 3/8" Stud Hole
 Spacing, Long Barrel, Tin Plated

Product Description

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	6 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7,374
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us