

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3925-09

Melon

Two-light flush mount with dome shaped alabaster glass, solid trim and decorative knobs. Center lock-up with matching finial.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel construction

Alabaster glass bowl



Diameter: 13-1/4"

Height: 5-7/8"

Glass: 9-13/16" dia.

Height: 3-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling flush mount</p> <p>Mounting strap for outlet box included</p> <p>Ceiling pan covers a standard 4" hexagonal recessed outlet box</p>	<p>Pre-wired</p> <p>Six inches of wire supplied</p> <p>120V</p>	<p>Quantity: 2</p> <p>75W Medium Base</p> <p>Medium ceramic sockets</p>	<p>cCSAus Damp location listed</p> <p>1 year warranty</p> <p>Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Sconce, Wall bracket, fixtures are available</p>