



Representative Image

Catalog No. TE100S

Description: ENCLOSURE NEMA 1 SURFACE 100A

UPC No 783164004915

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker. Spectra® RMS circuit breakers are suitable for use on AC systems only.

Frame notes and/or restrictions:2 and 3 pole only.

ACCESSORIES:

Neutral Kit (non-GF applications):included

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA Type 1
Mounting	Surface
Frame Type	E150, SE150
Amperage	100 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	208C2891SH3
GSA Compliance	No

Dimensions

Height	17.0 in
Depth	4.7 in
Width	7.9 in
Weight	9.4 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 1 enclosure, 100 amp max. Product Numbers TE100F and TE100S. 1 page outline drawing in .pdf format.	208C2891-SH3	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.