



GE  
Lighting

### 68185 - GE LED PAR38

LED26DP38S830/40

Energy-efficient LED lamps. Long life.

### Product Photo



### GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor and outdoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life - Min	25000 h
Rated Life (Hours)	25000 h
Bulb Shape	PAR38

### PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	3100 cd
Lumens per Watt (Efficacy)	58 lm
Nominal Initial Lumen per Watt	58
Rated Beam Spread	40 rad
Initial Lumens-nominal	1500 lm
Color Rendering Index-CRI	82
Color Temperature	3000 K

### PRODUCT INFORMATION

Product Code	68185
Description	LED26DP38S830/40
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168681858
Standard Package GTIN	10043168681855
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168681858
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168681858
Standard Package GTIN	00043168681858
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168681858

### ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	26 W

### CAUTIONS & WARNINGS

#### Caution

Risk of Electric Shock

Suitable for wet locations

Not intended for use with emergency exit fixtures or emergency exit lights

Performance may vary with electronic timers, photocells or dimmers

Use in totally enclosed fixtures may result in lower lamp life