

Rigid Non-Metallic Conduit Bodies & Covers

T&B Catalog Number:

E985G-CAR

UPC Number:

03448113245

Status:

Active

Description:

Type LR Conduit Body, Volume 32 Cubic Inches, Size 1-1/4 Inch, Length 7-31/32 Inches, Width 2-3/4 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit, Pack of 5

Features

Textured lids

Foam-in-place gasket

Application

For use with Rigid Conduit

General

Trade Size (inches)

1-1/4

Material

Non-Metallic

Volume (cu.in.)

32

Conduit Body Shape

LR

Dimension Information

C (inches)

1 3/32

H (inches)

2 5/16

L1 (inches)

7 31/32

L2 (inches)

6 13/32

L3 (inches)

6

Q (inches)

2 1/2

W (inches)

2 3/4

Packaging

T&B Order Multiple

5

Package in Units

5

T&B Sold in UOM

Each

T&B Weight Per UOM

0.83 lbs. Each

Application Support

Rigid Non-metallic Conduit Bodies

Available on Website

Specifications & Applications

Available on Website

Certifications



File Nbr:

E11461

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com

