



**Search Parameters:**

[e-Catalog](#) > [Switches & Disconnects](#) > [Disconnect & Safety Switches](#)

**Switches & Disconnects, Disconnect & Safety Switches**

Product #: TH3221R

Short Description: 30A 2P HD SS N3R 240V FUSIBLESWITCH

[Print This Page](#)

[Email This Page](#)

**SPECIFICATIONS**

Category	Heavy Duty
Voltage	240 AC
Amperage	30 A
Poles	2
Wires	3
Fusing	Fusible
Enclosure	NEMA 3R (Outdoor)
Options	None
Height	10.5 in
Depth	3.14 in
Width	6.2 in
Weight	7.0 lb
Wire Range (Cu/Al)	14-8 CU;12-8 AL
240 Vac, NEC Std, 1-ph	1 hp
240 Vac, NEC Std, 3-ph	3 hp
240 Vac, Time Delay, 1-ph	3 hp
240 Vac, Time Delay, 3-ph	7 hp
250 Vdc	5 hp
GSA Compliance	Yes
CSA Certified	Yes
UL Listed	Yes
GO Schedule	131
List Price	\$291



[View Larger](#)

**Publications/Resources**

[TH3221R](#)

**Additional Resources for Heavy Duty**

[Application and Technical Brochures](#)

[Drawings-Outline and Dimensional](#)

[BIM Files](#)

[Buy Log :2-8](#)

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.
- NEMA type 4X enclosure grade 304 stainless steel (catalog numbers with SS suffix).

