



Catalog No. TH4324

Description: 200A 3P HD N1 240V FUSIBLE SW

UPC No 783164009286

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	240 AC
Amperage	200 A
Poles	3
Wires	4
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	2-250
240 Vac, NEC Std, 1-ph	15.0 hp
240 Vac, NEC Std, 3-ph	25.0 hp
240 Vac, Time Delay, 3-ph	60.0 hp
250 Vdc	40.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	31.5 in
Depth	5.1 in
Width	13.3 in
Weight	33.0 lb

Publications

Title	Publication No.	Publication Type
200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH105	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.