

3 Light Semi Flush/Pendant - 42122NI

42122NI (Brushed Nickel)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	42122NI
Finish	Brushed Nickel
Available Finishes	NI, OZ

Dimensions

Base Backplate	4.75 DIA
Chain/Stem Length	36.00"
Weight	9.00 LBS

Specifications

Material	Steel
Glass Description	Satin Etched Tempered
Shade Description	White Micro Fiber
Shade Dimensions	5.50 X 24.00

Electrical

Voltage	120V
Lead Wire Length	74.00"

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Installation

Max Stem Tilt	90 Degrees
---------------	------------

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	3
Max or Nominal Watt	150W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	12.25"
Overall Height	44.00"
Width	24.00"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	32-50W		

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

