



Liquidtight Flexible Non-Metallic Conduit & Fittings

T&B Catalog Number:

15008-100

UPC Number:

03448123328

Status:

Active

Description:

1 Inch Gray Liquidtight Flexible Non-metallic Conduit, 100 Foot Coil

Features

Non-conductive and non-corrosive.
Lightweight for easy handling, transportation and installation.
Crush, abrasion and strain resistant.
Provides superior wire protection
Smooth interior ideal for pulling cable, no jagged edges.
Maintains internal I.D. even in tight radius bends.
Resistant to oil, acid, ozone, and alkaline.
UL listed for outdoor use and sunlight resistant.
UL listed for use as indicated in Article 356.2 of the NEC and Section 12-1300 of the Canadian Electrical Code, Part 1.
Suitable for use at conduit temperatures of 80 degree C dry, 60 degree C wet and 60 degree C oil resistant as required by Section 15-6 of ANSI/NFPA 79 and UL 1660.
Sequentially market footage

Application

Control and Motor
Air conditioning and heating
Computer power distribution
Machine Tools
Console wiring
Transformer connections
Outdoor lighting

General

Material	Non-Metallic
Color	Gray

Dimension Information

Size (inches)	1
Average O.D. (inches)	1.302
Average I.D. (inches)	1.046
Nominal Size (inches)	1
Coil Length (feet)	100

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	24.94 lbs. per 100

Application Support

Product Overview-Carflex Liquidtight Flex-Available on Website
ible Tubing

Notes

Available in black and gray.

Customer cut lengths available.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com