

## 430R7W



Color:  Red

UPC Code: 07847708552

## 430R7W

### Item Description

30 Amp, 480 Volt 3-Phase, 3P, 4W, Outlet North American Pin & Sleeve Receptacle, Industrial Grade, IP67, Watertight - RED

### Technical Information

#### Electrical Specifications

**Dielectric Voltage:** 3000V for 1 min.

**Temperature Rise:** Max 30C after 50 cycles OL at 150 percent rated current

**Voltage:** 480 Volt 3-Phase

**Current Interrupting:** Certified for current interrupting at full rated current

**Amperage:** 30 Amp

**Endurance:** Up to 1000 connects and disconnects, under load, at full rated current and voltage

**Wire:** 4

**Insulation Resistance:** 500V for 1 min;  $\geq 5M$

**Pole:** 3

#### Environmental Specifications

**Corrosion Resistance:** Ferrous parts immersed in 20°C, 10 percent ammonium chloride solution for 10 min

**Moisture Resistance:** Per UL 1682, immersed for 24 hours in 5cm of 25°C water

**IP Rating:** IP67, Watertight

**Flammability:** Rated V-2 per UL94

#### Material Specifications

**Body Material:** Valox 357

**Mounting Flange:** Valox 357

**Cover Eyelet:** Nickel-Plated Brass

**Terminal Screws:** Steel

**Arm Spring:** Performance Grade Stainless Steel

**Sleeve Spring:** Stainless Steel

**Cover with Arm:** Valox 357

**Gasket Material:** Chloroprene

**Phase and Ground Sleeves:** Brass

#### Mechanical Specifications

**Minimum Withdrawal Force:** 6lbs

**Crush Test:** 250lbs for 1 min after -25°C for 6 hrs

**Impact Resistance:** Drop from 30" 8 times after conditioning to -25°C for 6 hrs

#### Product Features

**Color:** Red

#### Standards and Certifications

**UL Listed:** 1682 and 1686


**Warranty:** 2-Year Limited

**IEC Rating:** 60309-1 and 60309-2


**CE Marking:** Per low voltage directives 73/23/EEC, 93/68/EEC

**CSA Certified:** C22.2 No 182.1

## Dimensional Diagram



UNIT	A	B	C
inch	2.20	2.40	4.10
mm	56	61	104



## SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

