



Representative Image

Catalog No. TQD32200WL

Description: TQD 3POLE 240V 10K IC200A W/LUGS

UPC No 783164021356

Products > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The TQD Line of devices include thermal magnetic molded case circuit breakers and molded case switches. The devices are complete with Cu/Al line and load lugs.

Descriptors

Category	Thermal Magnetic
GO Schedule	EF

Specifications

Product Line	Thermal Magnetic
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	200 A
Poles	3
System Voltage	120 Vac, 120/240 Vac, 240 Vac
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
240 Vac Interrupting Rating	10 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TCAL25
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Special Markings	HACR
GSA Compliance	Yes

Classifications

UL File #	E11592
-----------	--------

Publications

Title	Publication No.	Publication Type
TQD / THQD MCCB, 3- Pole 100-225 Ampere, Drawing 1 page, Fully Dimensioned Layout Drawing in .dxf format	455C765-SH1-DXF	Drawings-Outline and Dimensional
TQD / THQD MCCB, 3- Pole 100-225 Ampere, Drawing 1 page, Fully Dimensioned Layout Drawing in .pdf format	455C765-SH1	Drawings-Outline and Dimensional
TQD / THQD MCCB, 2- and 3- Pole 100-225 Ampere, Drawing 1 page, Non-dimensioned full scale layout drawing in .dxf format	TQD225 2-3P-DXF	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.