



Catalog No. TQL100R

Description: ENCLOSURE NEMA 3R 100A

UPC No 783164021417

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Frame notes and/or restrictions: THQL, TXQL, THQL-GF (1, 2, 3 Pole)

Enclosure notes and/or limitation: Enclosure cannot accommodate a 3-pole breaker with accessory.

Enclosure includes removable closing cap.

ACCESSORIES:

Neutral Kit (non-GF applications): included

Raintight Hubs: TC75, TC100, TC125, TC150, TCCP

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B3

Specifications

Enclosure Type	NEMA Type 3R
Mounting	Surface
Frame Type	Q-Line
Amperage	100 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5652SH1
GSA Compliance	Yes

Dimensions

Height	17.0 in
Depth	5.0 in
Width	6.9 in
Weight	10.5 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 3R enclosure, 125 amp max. Product Numbers TE100R, TQC100R, TQL100R, TQL100RE, and TQL125R. 1 page outline drawing in .pdf format.	139C5652-SH1	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.