



Powering Business Worldwide

pe.eaton.com

Type QCF 1/2-inch Quicklag Industrial Thermal-Magnetic Circuit Breaker

QCF1020

UPC: 786679143063

Dimensions: 4.6 IN * 3 IN * 1.2 IN (L * W * H)

Notes: Standard Breaker terminals are box type lugs. Switching duty rated for fluorescent lighting applications.

Warranty: 1 year

Specifications:

- **Type:** Quicklag
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Mounting:** Front
- **Trip Type:** Non-Interchangeable
- **Circuit Breaker Type:** QCF
- **Connection:** Cable-in/Cable-out

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

Certifications: No Data

Product compliance: No Data

