












# SAWZALL® BLADES

## SPECIALTY SAWZALL® BLADES

Description	TPI	Length	Height	Width	1 Pack	3 Pack	5 Pack	50 Pack	Bulk (100)
 <b>DUCTWORK</b>	30	3.33"	0.75"	0.050"	-	-	48-00-1630	-	-
 <b>DRYWALL ACCESS</b>	-	2.5"	0.75"	0.062"	48-00-1640	-	-	-	-
 <b>FLUSH CUT</b>	5	12"	2-1/8"	0.062"	48-00-1600	-	-	-	-
 <b>ROUGH-IN</b>	5	7-3/8"	1/2"	0.062"	-	-	48-00-1610	-	-
 <b>THE TORCH™ DIAMOND GRIT</b>	GRIT	6"	1"	0.042"	48-00-1440	-	-	-	-
	GRIT	9"	1"	0.042"	48-00-1450	-	-	-	-
 <b>CARBIDE GRIT</b>	GRIT	6"	3/4"	0.032"	48-00-1421	48-00-1420	-	48-01-6420	-
	GRIT	9"	3/4"	0.032"	48-00-1431	48-00-1430	-	48-01-6430	-
 <b>PRUNING</b>	5	9"	3/4"	0.049"	48-00-1304	-	48-00-1301	-	-
	5	12"	3/4"	0.049"	48-00-1305	-	48-00-1303	-	-
 <b>CLEAN WOOD</b>	6	6"	3/4"	0.050"	-	-	48-00-5015	-	48-01-7015
	6	9"	3/4"	0.050"	-	-	48-00-5016	-	48-01-7016
	6	12"	3/4"	0.050"	-	-	48-00-5017	-	-
 <b>PLASTER</b>	6	5"	3/4"	0.050"	-	-	48-00-5052	-	-
 <b>METAL SCROLLING</b>	10	3-5/8"	5/16"	0.035"	-	-	48-00-5161	-	-
	14	3-5/8"	5/16"	0.035"	-	-	48-00-5162	-	-
	18	3-5/8"	5/16"	0.035"	-	-	48-00-5163	-	-
 <b>WOOD SCROLLING</b>	4/6	6"	1/2"	0.050"	-	-	48-00-5041	-	-

**DIAMOND GRIT THE TORCH™**  
48-00-1440 and 48-00-1450



**IDEAL FOR CAST IRON**

**SCRAPER BLADES**  
19-98-5455, 49-00-5456 and 49-00-5463



**IDEAL FOR MATERIAL REMOVAL**

## SAWZALL® / HACKZALL™ UTILITY BLADES

	<b>Description</b>	<b>1 Pack</b>	<td><b>Description</b></td> <td><b>1 Pack</b></td> <td> <td><b>Description</b></td> <td><b>1 Pack</b></td> <td><b>Bulk (5)</b></td> </td>	<b>Description</b>	<b>1 Pack</b>	<td><b>Description</b></td> <td><b>1 Pack</b></td> <td><b>Bulk (5)</b></td>	<b>Description</b>	<b>1 Pack</b>	<b>Bulk (5)</b>
	<b>GROUT REMOVAL TOOL</b>	49-00-5450		<b>5\"</b>	19-98-5455		<b>3\"</b>	49-00-5456	49-01-5456
				<b>1-1/2\"</b>	49-00-5463		<b>1-1/2\"</b>	49-00-5463	49-01-5463

## HACKZALL™ BLADES

Application	Length	TPI	Product No.	Qty
WOOD	4"	6	49-00-5460	5
WOOD SCROLLING	3-1/2"	10	49-00-5310	5
METAL SCROLLING	3-1/2"	24	49-00-5324	5
FIBERGLASS	4"	grit	49-00-5400	3
MULTI-MATERIAL	4"	10	49-00-5410	5

Application	Length	TPI	Product No.	Qty
PVC	4"	14	49-00-5414	5
	6"	14	49-00-5614	5
EMT	4"	18	49-00-5418	5
DUCT	4"	24	49-00-5424	5
PLASTER AND DRYWALL	4"	6	49-00-5461	5

Designed to optimize the cutting performance of HACKZALL® recip saws.

Accessibility: Shorter blades allow access to tight spaces.

## SAWZALL® BLADE SETS

Product No.	49-22-5403	49-22-0240	49-22-1145	49-22-0220
<b>Description</b>	<b>3 PC MATERIAL REMOVAL SET</b>	<b>8 PC THIN KERF SAWZALL® BLADE SET</b>	<b>9 PC THIN KERF SAWZALL® BLADE SET</b>	<b>10 PC M12™ HACKZALL™ BLADE SET</b>
<b>Contents</b>	(1) 1-1/2" scraper blade (1) 3" scraper blade (1) grout removal tool	(2) 6" 5TPI Thin Kerf wood blades (2) 9" 5TPI Thin Kerf wood blades (2) 6" 14TPI Thin Kerf Ice Hardened™ metal blades (2) 6" 18TPI Thin Kerf Ice Hardened™ metal blades	(3) 6" 24TPI Thin Kerf metal blades (3) 6" 14TPI Thin Kerf metal blades (2) 6" 5TPI Thin Kerf wood blades (1) 9" 5TPI Thin Kerf wood blade	(2) wood blades (3) EMT blades (2) duct blades (3) PVC blades

## WOOD BORING SELECTION GUIDE

**1** Identify the material to be cut in the columns below

**2** Follow the column down to find **BEST PERFORMANCE** or **ACCEPTABLE PERFORMANCE**

	CLEAN WOOD	WOOD WITH NAILS	HOLE FINISH	FAST DRILLING	DRILLS POCKET HOLES	WIRE PULLING	IMPACT RATED
PG. 52 <b>SELFEED BIT</b>			ROUGH				
PG. 54 <b>BIG HAWG®</b>							
PG. 54 <b>SHIP AUGER</b>							
PG. 55 <b>SPUR AUGER</b>							
PG. 55 <b>SPEED FEED™</b>							
PG. 55 <b>FLAT BORING</b>							
PG. 56 <b>BRAD POINT</b>							
PG. 56 <b>FORSTNER</b>			FINE				
PG. 56 <b>BELLHANGER</b>							
PG. 56 <b>CABLE</b>							

## SWITCHBLADE™ SELFEED BITS

### LONG LIFE

- Cutting edge is replaceable, made with hardened steel to increase bit life

### FAST DRILLING

- Aggressive feed screw design allows the bit to pull through the wood faster

### EASY SIZE REFERENCE

- Bit and blades are engraved with quick and easy size identification

### SWITCHBLADE™



Size	Part Number	Qty	Shank Type	Entrance For Pipe and Rigid Conduit	Entrance For Tubing
1-3/8"	48-25-5120	1	7/16" Hex	1"	1-1/4"
1-1/2"	48-25-5125	1	7/16" Hex		1-3/8"
2"	48-25-5135	1	7/16" Hex	1-1/2"	1-7/8"
2-1/8"	48-25-5140	1	7/16" Hex		2"
2-1/4"	48-25-5143	1	7/16" Hex		2-1/8"
2-9/16"	48-25-5150	1	7/16" Hex	2"	2-1/2"

## SWITCHBLADE™ SELFEED BIT KIT



### 5 Pc SWITCHBLADE™ Plumber's Kit 49-22-5100

#### Includes:

- (1) Each SWITCHBLADE™ selffeed bits (1-3/8", 1-1/2", 2-1/8", 2-9/16")
- (1) 5-1/2" QUIK-LOK™ extension
- (1) Each replacement blades
- (4) Feed screws
- (4) Set screws
- (1) Hex wrench
- Case with bulk storage container

## SWITCHBLADE™ REPLACEMENT BLADES

Size	Part Number	Qty	Size	Part Number	Qty
1-3/8"	48-25-5420	1	2-1/8"	48-25-5240	3*
1-1/2"	48-25-5425	1	2-9/16"	48-25-5250	3*
2"	48-25-5435	1	1-3/8"	48-25-5320	10*
2-1/8"	48-25-5440	1	1-1/2"	48-25-5325	10*
2-1/4"	48-25-5443	1	2"	48-25-5335	10*
2-9/16"	48-25-5450	1	2-1/8"	48-25-5340	10*
1-3/8"	48-25-5220	3*	2-9/16"	48-25-5350	10*
1-1/2"	48-25-5225	3*			
2"	48-25-5235	3*			

\*Includes hex wrench and case



Replacement Feedscrew Pack  
48-25-5275



SWITCHBLADE™ Accessory Service Kit  
48-25-5280