



Actual

**Catalog Number:** 54740  
**Product ID:** 7TAH007300R0015  
**UPC Number:** 78621054740  
**EAN Number:** 05414363144113  
**Status:** Active

Copper C-Tap for 600V Applications, Wire Range Main: 2-1/0, Branch 2-12, Length 1-1/16 Inches, Height 31/32 Inch, Plain Finish, Die Code 50, Die Color Code Orange

- Positive, all-around compression with low resistance and high pull-out values.
- Ideal for pigtailing, 2-way splicing or tapping to an unbroken continuous main.
- Heavy reinforcing ribs help locate compression dies and strengthen compressed joint.

### North American Specifications (UNSPSC)

UNSPSC	39121428 Electrical taps
IGCC	4600 Electrical taps
Brand Name	Color-Keyed
Type	C-Tap
Special Features	Positive, all-around compression with low resistance and high pull-out values.
Standard	UL E9809
Conductor Size	2-1/0
Tap Size	2-12
Voltage Rating	600V
Material	Copper
Finish	Plain

### Packaging

Inner Quantity	1
Outer Quantity	50
Outer Dimensions (inches)	6.3x4.9x3.5
Weight Uom	9 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00628-tb2

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)