



BURNDY Catalog Number BIBD6005
 UPC Number 781810224175
 Description 600-4 TWO SIDED UNITAP
 Status Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 3
 Hex Size (Key) 3/8
 Length (in) 6.17
 Height (in) 2.75

Electrical

Min Voltage Rating 600

General

Number of Ports 5
 Number of Screws 5
 Product Description Aluminum Multiple Tap
 Connector, Clear Insulated, 5 Port,
 2 Sided Entry, 4 AWG-600 kcmil,
 Al/Cu Rated

Conductor(s)

Aluminum Size (Range) 4 AWG-600 kcmil
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 4 AWG-600 kcmil

Physical

Type of Hardware Aluminum
 Type of Plating Unplated
 Insulation Type Plastisol
 Plated (Yes or No) N
 Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175