

SED SERIES FAN-FORCED WALL HEATER



IDEAL SPACES

- Bedrooms
- Living/Family Rooms
- Kitchens
- Bathrooms
- Basements
- Offices
- Conference Rooms
- Hallways
- Lobbies
- Waiting Rooms

COLORS

- Northern White
- Stainless Steel

DIMENSIONS

- Grille: 14-1/2"H x 10-1/2"W x 1-1/4"D
- Back Box: 12-1/2"H x 9"W x 2-3/8"D

TEMP RANGE

- 45°– 90°F

CFM

- 50



- Ideally suited for recessed shallow wall mount applications such as manufactured homes
- Fast response open coil element for instantaneous heat and low maintenance
- Dual Protection: Thermal cutout with indicator light and one-time thermal fuse
- Field wiring compartment for ease of installation
- Built-in double-pole thermostat on all units
- Ceiling-mount units (1,000 watt units) and surface-mount accessories available



SED SERIES

FAN-FORCED WALL HEATER

MODELS & SPECIFICATIONS

CATALOG NO.	UPC	VOLTS	WATTS	AMPS	CEILING MOUNT	SHIP WT. (LBS.)
SED1012C*	6 85360 08190 8	120	1000	8.3	Yes	12
SED1024C*	6 85360 08191 5	240/208	1000/750	4.2/3.6	Yes	12
SED1512	6 85360 08192 2	120	1500	12.5	No	12
SED2024	6 85360 08193 9	240/208	2000/1500	8.3/7.2	No	12
SED1012W	6 85360 14888 5	120	1000	8.3	Yes	12
SED1024W	6 85360 15698 9	240/208	1000/750	4.2/3.6	Yes	12

NOTE: *Stainless steel models.

ACCESSORIES

CATALOG NO.	UPC	DESCRIPTION	SHIP WT. (LBS)
SEDSM	6 85360 01043 1	Northern White Surface Mounting Frame	3
SEDSMC	6 85360 12617 3	Stainless Steel Surface Mounting Frame	3
SEDFCW	6 85360 12616 6	Front Cover - Northern White	2
SEDFCC	6 85360 12615 9	Front Cover - Stainless Steel	2