



Product Specifications for E21310-10PC

Job Name:	Job Type:
Quantity:	Comments:



**E21310-10PC**  
**Inca 9-Light Pendant**

**Finish**  
Polished Chrome

**Glass/Shade**  
Clear/White

**Product Category**  
Linear Pendant

**Lamping**

Number of Bulb(s)	9
Light Type	Xenon
Bulb Type	G9
Max Bulb Wattage	40
Max Fixture Wattage	360
Rated Life	±2,000 Hours
Rated Lumens	±4,500
Color Temp	±2,900 K
Bulb(s) Included	Yes
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	No
Dimmable	Standard

**Measurements**

Width	12.00"
Height	10.00"
Length	31.50"
Extension	N/A
Back Plate Width	N/A
Back Plate Height	N/A
HCO	N/A
Min Overall Height	N/A
Max Overall Height	120.00"
Hanging Weight	12.76 lb(s)
Height Adjustable	Yes
Slope	N/A
Chain Length	N/A
Wire Length	130.00"
Canopy Width	5.0"
Canopy Height	1.0"
Canopy Length	10.0"

**Shipping**

Carton Weight	17.60 lb(s)
Carton Width	15.75"
Carton Height	14.57"
Carton Length	34.65"
Carton Cubic Feet	N/A
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

**Certification**

Safety Rating	Dry
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No

**Other**

UPC Code	845094045403
Material	Metal

**Equivalents**

Incandescent Watts	N/A
Fluorescent Watts	N/A

ET2 Contemporary Lighting and all designs, logos and images © 2014 ET2 Contemporary Lighting. All Rights Reserved. ET2 Contemporary Lighting reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes. Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.