



Measurements:

<u>Height</u>	<u>Width</u>		
23.50"	26.00"		
<u>Max OAH</u>			
22.55"			
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
11.03 lb	5.00"	1.00"	5.00"

Lamping:

Incandescent MB Incandescent 5,750 Rated Lumens
 5.00 100W MB Incandescent Color Temperature
 500 total watt 2,500 Rated Life
 Dimmable : Standard

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
17.83 lb	21.65"	9.84"	26.18"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209025882	Yes	

Finish:

Satin Nickel SN

Glass:

Ice IC

Material:

Steel

Certification:

Dry Location
 Location

Additional:

MB Incandescent (Not Included)