



31161-05: Five Light Chandelier



Collection: Oslo

UPC #:785652171475

Finish: Chrome (05)

Dimensions:

Diameter: 24" **Overall Height:** 152 1/2"
Height: 20" **Wire:** 144" (color/Clear Silver)
Weight: 9.3 lbs. **Chain:** 120"
Mounting Proc.: Center Lock-Up

Bulbs:

5 - Medium A19 100w Max. 120v - Not included

Features:

- Adjustable arms rotate for up or down lighting
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Material List:

1 Chain - Steel - Chrome
 1 Body - Steel - Chrome

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1901FS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Cased Opal Etched	5				5 29/32	3 15/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	13/16			5 1/2		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	31161-05	1	785652171475	20.125	20.75	8.75	2.115	11.8	175	Yes
NJ Pallet		32		48	40	76	84.444	377.6		No
NV Pallet		30		48	40	70	77.778	377.6		No