

Job Name:		Item Number:	
Specifier Name:		Sales Agency:	
Specifier Contact:		Agency Contact:	
Fixture Type:		Comments:	
Quantity:		Approval:	

12V Directional LED Module 3000K 60° Beam



Description

Specifications

Item Number	98327S-15
Finish	White
Dimensions	L: 2" W: 1 5/16" H: 1 3/4"
Voltage	12V
Light Source	LED
Color Temperature	3000°K
Lumens	65
Watts Consumed	1.4 watts
Efficacy	46.4 lm/w
Color Rendering	>90 CRI
Rated Average Life	50,000 hours to 70%

Instruction Sheets

- Trilingual (English, Spanish, and French) (990LXDIRECT)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98327S-15	1	785652276101	3.5	2.75	2.75	0.015	0.1	Yes
Master Pack	98327S-15	6	10785652276108	9	6	4	0.125	0.9	Yes