

SECURITY AND ALARM CABLE

CL3R -Nonshielded Conductors
PVC Insulation & Jacket
300 Volt -14 AWG & 12 AWG

CONSTRUCTION	
Conductor	- Stranded bare copper to ASTM B-3, B-8, and B-286
Insulation	- Color coded PVC
Jacket	- PVC - Includes ripcord

Applications:

- Power limited control circuits
- Wiring of the following systems:
- Intercom
- Security
- Audio
- Suggested Voltage Rating: 300 Volts

Standards:

NEC Article 725 Type CL3R

PART #	AWG	CONDUCTORS	INSULATION THICKNESS	JACKET THICKNESS	NOM. O.D.	LBS./M'
DS91402	14	2	.013"	.015"	.223"	38
DS91403	14	3	.013"	.015"	.239"	54
DS91404	14	4	.013"	.015"	.245"	65
DS91202	12	2	.014"	.020"	.280"	54.9

Note: The data shown is approximate and subject to standard industry and



manufacturer tolerances. 01-05-2017

Color Code Chart	
Cond. #	Color
1	Black
2	Red
3	White
4	Green