



GE  
Lighting

42144 - null

LED12DP3LRW82740

Product Photo



**GENERAL CHARACTERISTICS**

Primary Application	Track & Recessed
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26

**PHOTOMETRIC CHARACTERISTICS**

Beam Spread (range)	40 deg
Center Beam Candle Pwr Candela	2200 cd
Nominal Initial Lumen per Watt	83.3
Rated Beam Spread	40 deg
Initial Lumens-nominal	1000 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

**PRODUCT INFORMATION**

Product Code	42144
Description	LED12DP3LRW82740
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168421447
Standard Package GTIN	10043168421444
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168421447
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168421447
Standard Package GTIN	00043168421447
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168421447

**DIMENSIONS**

Bulb Max Overall Length-MOL	4.72 in
-----------------------------	---------

**ELECTRICAL CHARACTERISTICS**

Voltage <Nom>	120 V
Input Voltage [nom]	120 V