



## Sunlite 50 Watt, 38° Flood, MR16 Mini Reflector, GU5.3 Bi-Pin Base

Sunlite Halogen bulbs produce more lumens per-watt (LPW) and have a longer lamp life than standard incandescent lamps. You can lower operation costs by more than 30% by using fewer halogen lamps to produce a greater amount of light. These MR16 GU5.3 Based Mini Reflector bulbs can last up to 1.8 years with normal household use of 3 hours a day and display a brighter, whiter light than incandescent bulbs. This Sunlite 50-watt, MR16 GU5.3, based Mini Reflector bulb offers a light output of 1500 CBCP and has an average rated life of 2000 hours. Great for portable lamps, ceiling fixtures, track lighting, showcase displays and most common lighting needs.

- 50-Watt, 1500 CBCP
- 2,000 Hour Average Lamp Life
- GU5.3 base, EXN
- Open cover
- 50MR16/FL/12V

### General Characteristics

<b>Bulb</b>	MR16
<b>Lamp Type</b>	MR16 Mini Reflector
<b>ANSI CODE</b>	EXN
<b>Lamp Life Hours</b>	2,000 Hours
<b>Base</b>	GU5.3
<b>Lumens Per Watt (LPW)</b>	30.00
<b>Life (based on 3hr/day)</b>	1.8 Years
<b>Estimated Energy Cost</b>	\$6.02 per Year
<b>Dimmable</b>	True

### Electrical Characteristics

<b>Watts</b>	50
<b>Volts</b>	12

### Light Characteristics

<b>Brightness</b>	1500 Lumens
<b>Color Accuracy (CRI)</b>	100
<b>CBCP</b>	1500
<b>Coating</b>	UV Protected
<b>Light Appearance</b>	Bright White
<b>Color Temperature</b>	3200K
<b>Beam Angle</b>	38° Flood

### Product Dimensions

<b>MOL (in)</b>	1.756"
<b>Diameter (in)</b>	1.952"
<b>Item Dimensions (in)</b>	(W) 1.97 (H) 1.76 (D) 1.97
<b>Package Dimensions (in)</b>	(W) 2.00 (H) 2.10 (D) 2.10

### Product Data

<b>Item Number</b>	03210-SU
<b>Case Quantity</b>	24
<b>Barcode on SKU</b>	653703032108
<b>Barcode on Case</b>	10653703032105
<b>Brand</b>	SUNLITE
<b>Description</b>	50MR16/FL/12V

