



Powering Business Worldwide

pe.eaton.com

SVX Independent Drives

SVX007A1-4A1B1

UPC:782116011483

Dimensions:

- **Height:** 16.5 IN
- **Length:** 8.4 IN
- **Width:** 5.6 IN

Weight:17.9 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR5
- **Horsepower:** 7.5 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480V

Supporting documents:

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Product Datasheet - SVX007A1-4A1B1](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX_\(FR5\) AutoCAD 2D Footprint](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [SVX_\(FR5\) 3D Inventor](#)
- [SVX_\(FR5\) 2D PDF](#)
- [SVX_\(FR5\) 2D Drawing Xchange](#)
- [SVX_\(FR5\) AutoCAD 2D Footprint \(mm\)](#)
- [SVX_\(FR5\) 3D Model Xchange](#)
- [9000X AFD User Manual](#)



- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX007A1-4A1B1](#)

Certifications:

- IEC 61800-2
- EN 61800-3 Level H
- UL 508C

Product compliance: No Data