



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Heavy Duty Safety Switch

DH363FRK

UPC: 782113206424

**Dimensions:** 22.5 IN \* 12.75 IN \* 9 IN (L \* W \* H)

**Notes:** Suitable for service entrance use with a Neutral Kit installed

**Warranty:** Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 30 at 480 Vac TD 1 Ph, 40 at 600 Vac TD 1 Ph, 60 at 480 Vac TD 3 Ph, 75 at 600 Vac TD 3 Ph

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Drawing Dataset](#)
- [Heavy-Duty Safety Switch with Busmann CUBEFuse Fuse Clips](#)
- [Eaton Specification Sheet - DH363FRK](#)

**Certifications:** No Data

**Product compliance:** No Data



