



GE
Lighting

21231 - null

LED4DCAC-C3/827

Product Photo



GENERAL CHARACTERISTICS

Primary Application	Deco
Product Technology	LED
Rated Life (Hours)	15000 h
Base	E12

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	75
Initial Lumens-nominal	300 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	21231
Description	LED4DCAC-C3/827
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168212311
Standard Package GTIN	10043168212318
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168212311
Alternative Unit Of Measure	EACH
Standard Package Quantity	48
Ean UPC	043168212311
Standard Package GTIN	00043168212311
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	48
Sales Unit	Each
UCC	043168212311
Alternative Unit Of Measure	PACK
Standard Package Quantity	
Ean UPC	043168212311
Standard Package GTIN	30043168212312
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Inner Pack
UCC	043168212311

DIMENSIONS

Bulb Max Overall Length-MOL	4.3 in
-----------------------------	--------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V