

iTOOLco.

CANNON 6K™

Faster

- 6000 lb. Pulling capacity
- Two pullers in one 3K / 6K
- 4 Speeds with dual capstans:
 - 8' & 28' FPM 6k side
 - 20' & 70' FPM 3k side

Safer

- No anchoring required (but bolt holes are provided on the base)
- Easy to transport and use on or off the cart
- Telescoping
- User can stand to either side during pulls
- Easily maneuvers into tight spaces
- Usable in the receiver hitch of a truck

Smarter

- No disassembly, fully self-contained no gang box full of parts
- Pivoting head for easy adjustment for underground, overhead, or side pulls
- Swivel locking hitch pins
- Recommended low stretch pulling rope size 5/8" or 9/16" with a minimum breaking strength of 15,000 lb.
- Easily extend boom with 2.5" rigid conduit

Includes

- Cannon 6K™ cable puller (weight 115 lb. including the motor)
- Super duty cart with adapters (weight 48 lb.)
- Length (fully extended) 9'3"
- No assembly required (Ships boxed & ready to use)
- Universal adapter
- 5 Conduit adapters sizes 2" through 4" (5" & 6" also available)
- Milwaukee 1680-20 power motor, 2 speed, 13 Amp, field replaceable, with 6 year limited warranty
- Foot switch (UL standard)

NOTE: Patent Pending

Model	Description
C6K	Cannon 6K - 6,000 lb. Wire Puller



6
YEAR
LIMITED
WARRANTY

MADE IN THE
USA
WITH GLOBAL
COMPONENTS

TWO PULLERS IN ONE — Hi-Speed 3K / Hi-Torque 6K

iTOOLco.

865-670-3713 • iTOOLco.com

Innovative Tools For Professional Electricians & Contractors

150818_FL_iTOOLco2