



Lamps

Ballasts

Luminaires

Company

Customer Care

Contact Us



Search > Results for F39T5/835/HO/ECO/IC > F39T5/835/HO/ECO/IC 35061 105620 F39 T5 3500K 85CRI HO IC



F39T5/835/HO/ECO/IC 35061 105620 F39 T5 3500K 85CRI HO IC

Product Number: 35061

UPC: 807154350612

[Log In for Price and Availability](#)

Note: this product is only sold in multiples of 25 items

Specifications	Resources	Technical
Applications	Cove lighting, Display Lighting, Indirect fixtures, High Bay Fixture	
Average Life (Hrs)	24000	
Base	Miniature Bi-Pin	
Brand	ProLume	
Bulb	T5	
CRI	86	
Color Temperature	3500	
Cross Reference - Osram Sylvania	FP39/835/HO/ECO	
Design Lumens	3320	
Dimmable	Yes	
HTS code	8539310070	
Initial Lumens	3500	
Input Frequency (Hz)	60	
Markets	Residential, Commercial	
Master Carton Quantity	25	
Maximum Overall Diameter	0.63	
Maximum Overall Length	34	
Nominal Length	34	
Operating Position	Universal	
Prod Code	F39T5/835/HO/ECO/IC	
Product Category	Linear Fluorescent	
Product Description	F39 T5 3500K 85CRI HO IC	
Product Number	35061	
Start Type	Programmed Start	
Warranty (Yrs)	2; 3 When Installed with ProLume Ballast	
Wattage (W)	39	

Products

Lamps



Ballasts



Luminaires



Resources

[Catalogs](#)
[Sell Sheets](#)
[New Products](#)

Contact Us

Corporate Office:
Halco Lighting Technology
2940 Pacific Drive
Norcross, GA 30071
Toll Free: 800.677.3334
Office: 770.242.3612
Fax: 800.880.0822
Email: customer care@halco.com



