



Hoffman

Screw-Cover, Type 1

Catalog Number: ASE10X10X6
US List Price (USD): \$33.51

Bulletin Number:

- A90P1

Material:

- Steel



Model Code:

- 43200

Ship Wt. Std. Pkg. (lbs):

- 8.0

Interchangeable:

- False

IP Rating:

- IP30

Industry Standards:

UL 50, 50E Listed; Type 1; File No. E27525 cUL Listed per CSA C22.2 No 40; Type 1; File No. E27525 NEMA/EEMAC Type 1 IEC 60529, IP30

Description

Applications:

Use this enclosure in commercial and general industrial applications that require a junction or pull box. For flush installations, order flush covers and door frames separately.

Features:

- Unique keyhole screw slots in the cover
- Available with or without knockouts. Various sizes of easy-to-remove concentric knockouts on all four sides of standard boxes with knockouts.
- Optional flush-mounted door frame available
- Optional flush covers
- Flat, removable covers fastened with plated steel screws
- Provision for grounding
- Mounting holes on back of box

Specifications:

16, 14 or 12 gauge steel or plated steel

Finish:

ANSI 61 gray polyester powder paint finish inside and out. Unless otherwise specified, all custom pull boxes are finished with ANSI 61 gray polyester powder paint.

Accessories:

- Flush Covers
- Flush-Mount Door Frames
- Grounding Device
- Type 1 Locking Window Pull Box Accessory
- Touch-Up Paint

Technical Data

Screw-Cover, Type 1

Catalog Number	ASE10X10X6
A in.	10
B in.	10
C in.	6
Style	Painted
Number of Cover Screws	4
Knockout Pattern along A Sides	F-G-H-I
Knockout Pattern along B Sides	C-D-E-F-G

Certifications



EU Certification



UL Certification

Documents



DOC



Spec Sheet



2D DXF CAD



3D STEP CAD



Dimension Drawing

Accessories

Item		
	Screw-Cover Pull Box Extender, Type 1	A10104SU
